


ポケットルーペ

NPL-50/NPL-25


この度は、ポケットルーペをお買い上げ頂きまして、誠にありがとうございます。
ご使用に際し、本説明書を最後までお読みいただき、正しい使い方でお使いいただきますようお願い申し上げます。

■焦点の合わせ方



- ①アクリル部の先端を対象物に垂直に当てます。
- ②接眼部をのぞきながら、アクリル部の先端を支点に、前後に傾けてピントを合わせてください。

⚠️ ご注意 構造上、目に映る画像は上下が逆になります。



■仕様

品番	倍率	視野	有効径	レンズ材質	本体サイズ	質量
NPL-50	50倍	2mm	6.8mm	ガラス	φ13× L125mm (クリップ除く)	約229g
NPL-25	25倍	3mm				

■特長

- クリップ付きで携帯に便利な高倍率ルーペです。

■ご使用にあたって

⚠️ 警告

- ルーペを通して太陽やスポットライト、サーチライトなどの強い光を絶対に見ないでください。失明の恐れがあります。
- ルーペを通して太陽光や強い光を体に当てないでください。やけどの恐れがあります。
- ルーペを直射日光及び反射光の当たる場所に放置しないでください。発火の恐れがあります。

⚠️ 注意

- 落としたりぶつかけたりしないでください。
- 雨の中や湿気が多い場所、高温・低温環境下、直射日光の当たる場所での使用、保管はおやめください。
- レンズの表面の汚れは強くこするとレンズに傷をつける恐れがありますので、柔らかい布で軽く拭き取ってください。
- 本製品の用途以外のご使用は、事故やけがの原因になりますので、絶対におやめください。

NSK 新潟精機株式会社

〒955-0055 新潟県三条市塚野目5丁目3番14号
☎ (0256)33-5502(代) FAX (0256)33-5528
URL <https://www.niigataseiki.co.jp>
I484-K 2501

CLIP LOUPE

NPL-50 / NPL-25


Thank you for purchasing the Clip Loupe.

Please read this manual thoroughly before use to insure proper operation and long service.


FEATURES

- High-magnification loupe with clip to keep it handy and secure.

FOCUSING



- ① Rest the Acrylic Tip on the object and hold the Loupe perpendicular to the surface.
- ② Look through the eyepiece and adjust focus by pivoting the Loupe on the tip to adjust distance.



- ⚠ CAUTION** The image seen in the eyepiece is reversed.

SPECIFICATIONS

Model No.	Magnification	Field of View	Effective Diameter	Material	Dimensions	Weight
NPL-50	50×	2 mm	6.8 mm	Lens: Glass	φ13×L125mm (excluding Clip)	approx.22g
NPL-25	25×	3 mm				

PRODUCT NOTES

⚠ CAUTION

- Never look at sun or strong light through the Loupe, there is risk of eye damage.
- Do not expose skin to sunlight or strong light through the Loupe, there is risk of burns.
- Do not leave Loupe in direct or indirect sunlight, there is risk of fire.

⚠ NOTICE

- Handle with care. Please protect from strong forces or shock.
- Please do not use or store instrument in rain or locations with excessive humidity. Do not use or store at extreme high or low temperatures. Keep out of direct sunlight.
- Clean lens with lens cloth and use gentle motion to prevent dirt from scratching surface.
- Use only as directed; improper use may cause accident or injury.

NSK Niigata Seiki Co., Ltd.

5-3-14, Tsukanome, Sanjo, Niigata, Japan, 955-0055
 Tel. : +81-256-33-5522 Fax. : +81-256-33-5518
 MAIL intl.sales@niigataseiki.co.jp
 URL <https://www.niigataseiki.co.jp>